



### Caratteristiche

<b>Tipo</b>	Anello antiestrusore
<b>Pressione d'esercizio</b>	fino a 500 bar
<b>Temperatura min.</b>	-50 °C
<b>Temperatura max.</b>	130 °C
<b>Mezzi</b>	Oli minerali HFA, HFB
<b>Montaggio</b>	in locali di montaggio chiuso
<b>Materiale</b>	PBTB (Poliestere 55 Shore D)



Spaltmaß / Clearance	
Druck / Pressure	e max.
250 bar	0,25
300 bar	0,20
350 bar	0,15
400 bar	0,10
500 bar	0,05



d (Oring)	g	L1	L2	e
2,40	2,00	4,60	5,90	1,30
3,00	2,50	5,40	6,70	1,30
3,70	3,00	6,20	7,50	1,30

### Nota

Misura della luce:  
 Pressione = 250 bar / e max.= 0,25  
 Pressione = 300 bar / e max.= 0,20  
 Pressione = 350 bar / e max.= 0,15  
 Pressione = 400 bar / e max.= 0,10  
 Pressione = 500 bar / e max.= 0,05

### Descrizione

semplice montaggio.  
 non occorre tagliare gli anelli  
 Soluzione conveniente.

### Articolo

Denominazione	M (mm)	N (mm)	e (mm)	OR
MBK 4 8	4,0	8,0	1,3	3,30 x 2,40
MBK 6 10	6,0	10,0	1,3	5,30 x 2,40
MBK 7 11	7,0	11,0	1,3	6,30 x 2,40
MBK 10 14	10,0	14,0	1,3	9,30 x 2,30
MBK 11 15	11,0	15,0	1,3	10,30 x 2,40
MBK 12 16	12,0	16,0	1,3	11,30 x 2,30
MBK 13 17	13,0	17,0	1,3	12,30 x 2,40
MBK 14 18	14,0	18,0	1,3	13,30 x 2,40
MBK 15 19	15,0	19,0	1,3	14,30 x 2,40
MBK 16 20	16,0	20,0	1,3	15,30 x 2,40
MBK 17 21	17,0	21,0	1,3	16,30 x 2,40
MBK 18 22	18,0	22,0	1,3	17,30 x 2,40
MBK 20 25	20,0	25,0	1,3	19,20 x 3,00
MBK 23 28	23,0	28,0	1,3	22,20 x 3,00
MBK 25 30	25,0	30,0	1,3	24,20 x 3,00
MBK 27 32	27,0	32,0	1,3	26,20 x 3,00
MBK 30 35	30,0	35,0	1,3	29,20 x 3,00
MBK 35 40	35,0	40,0	1,3	34,20 x 3,00
MBK 40 45	40,0	45,0	1,3	39,20 x 3,00
MBK 40 50	40,0	50,0	1,7	39,20 x 5,70
MBK 45 50	45,0	50,0	1,3	44,20 x 3,00
MBK 45 55	45,0	55,0	1,7	44,20 x 5,70
MBK 50 55	50,0	55,0	1,3	49,50 x 3,00
MBK 50 60	50,0	60,0	1,7	49,20 x 5,70
MBK 53 63	53,0	63,0	1,7	52,20 x 5,70
MBK 55 65	55,0	65,0	1,7	54,20 x 5,70
MBK 55 60	55,0	60,0	1,3	54,50 x 3,00
MBK 58 63	58,0	63,0	1,3	57,20 x 3,00
MBK 60 65	60,0	65,0	1,3	59,50 x 3,00
MBK 60 67	60,0	67,0	1,5	39,20 x 5,70
MBK 60 70	60,0	70,0	1,7	59,20 x 5,70
MBK 63 68	63,0	68,0	1,3	62,20 x 3,00
MBK 65 70	65,0	70,0	1,3	64,50 x 3,00
MBK 65 75	65,0	75,0	1,7	64,20 x 5,70
MBK 69 74	69,0	74,0	1,3	69,00 x 3,00



### Articolo

Denominazione	M (mm)	N (mm)	e (mm)	OR
MBK 70 75	70,0	75,0	1,3	69,50 x 3,00
MBK 70 77	70,0	77,0	1,5	39,20 x 5,70
MBK 70 80	70,0	80,0	1,7	69,20 x 5,70
MBK 72 77	72,5	77,5	1,3	72,00 x 3,00
MBK 72 82	72,5	82,5	1,7	71,20 x 5,70
MBK 75 80	75,0	80,0	1,3	74,50 x 3,00
MBK 75 85	75,0	85,0	1,7	74,20 x 5,70
MBK 78 88	78,0	88,0	1,7	87,20 x 5,70
MBK 79 84	79,0	84,0	1,3	78,00 x 3,00
MBK 80 85	80,0	85,0	1,3	79,50 x 3,00
MBK 80 87	80,0	87,0	1,5	39,20 x 5,70
MBK 80 90	80,0	90,0	1,7	79,20 x 5,70
MBK 85 90	85,0	90,0	1,3	84,50 x 3,00
MBK 85 95	85,0	95,0	1,7	84,20 x 5,70
MBK 90 95	90,0	95,0	1,3	89,50 x 3,00
MBK 90 100	90,0	100,0	1,7	89,20 x 5,70
MBK 92 99	92,5	99,1	1,4	92,00 x 4,00
MBK 94 99	94,0	99,0	1,3	93,00 x 3,00
MBK 95 100	95,0	100,0	1,3	94,50 x 3,00
MBK 95 105	95,0	105,0	1,7	94,20 x 5,70
MBK 100 105	100,0	105,0	1,3	99,50 x 3,00
MBK 100 110	100,0	110,0	1,7	99,20 x 5,70
MBK 105 110	105,0	110,0	1,3	104,50 x 3,00
MBK 105 115	105,0	115,0	1,7	104,20 x 5,70
MBK 110 115	110,0	115,0	1,3	109,50 x 3,00
MBK 110 120	110,0	120,0	1,7	109,20 x 5,70
MBK 113 118	113,0	118,0	1,3	112,00 x 3,00
MBK 115 120	115,0	120,0	1,3	114,50 x 3,00
MBK 115 125	115,0	125,0	1,7	114,20 x 5,70
MBK 120 125	120,0	125,0	1,3	119,50 x 3,00
MBK 120 130	120,0	130,0	1,7	119,20 x 5,70
MBK 125 130	125,0	130,0	1,3	124,50 x 3,00
MBK 125 135	125,0	135,0	1,7	124,20 x 5,70
MBK 130 135	130,0	135,0	1,3	129,50 x 3,00
MBK 130 140	130,0	140,0	1,7	129,20 x 5,70
MBK 135 140	135,0	140,0	1,3	134,50 x 3,00
MBK 135 145	135,0	145,0	1,7	134,20 x 5,70
MBK 140 145	140,0	145,0	1,3	139,50 x 3,00
MBK 140 150	140,0	150,0	1,7	139,20 x 5,70
MBK 142 151	142,0	151,0	1,8	-
MBK 145 150	145,0	150,0	1,3	144,50 x 3,00
MBK 145 155	145,0	155,0	1,7	144,20 x 5,70
MBK 150 160	150,0	160,0	1,7	149,20 x 5,70
MBK 152 161	152,0	161,0	1,8	-
MBK 155 165	155,0	165,0	1,7	154,20 x 5,70
MBK 160 170	160,0	170,0	1,7	159,20 x 5,70
MBK 165 175	165,0	175,0	1,7	164,20 x 5,70
MBK 170 180	170,0	180,0	1,7	169,20 x 5,70
MBK 175 185	175,0	185,0	1,7	174,20 x 5,70
MBK 180 190	180,0	190,0	1,7	179,20 x 5,70
MBK 185 195	185,0	195,0	1,7	184,20 x 5,70
MBK 190 200	190,0	200,0	1,7	189,20 x 5,70
MBK 195 205	195,0	205,0	1,7	194,20 x 5,70
MBK 200 210	200,0	210,0	1,7	199,20 x 5,70
MBK 210 220	210,0	220,0	1,7	209,20 x 5,70
MBK 220 230	220,0	230,0	1,7	219,20 x 5,70
MBK 230 240	230,0	240,0	1,7	229,20 x 5,70
MBK 240 250	240,0	250,0	1,7	239,20 x 5,70
MBK 250 260	250,0	260,0	1,7	249,20 x 5,70
MBK 270 280	270,0	280,0	1,7	269,20 x 5,70