

PN FS

Pritisna nazuvica, BES

HANSA FLEX

Osobine

Oblast primene	Pritisna nazuvica za creva HD 100 do HD 400, KP, TE
Priključak 1	Cevni nastavak
Oblik zaptivke 1	Priključak za rezni prsten
Skraćenica	BES
Norma	ISO 8434-1
Serijska	težak
Materijal	čelik
Površinska zaštita	galvanska prevlaka



Napomena

Završna montaža reznim prstenom mora se obaviti u kaljenom nastavku za predmontažu (VOM...).

Odgovarajući priključak molimo da odaberete prema tipu creva.

Ne koristiti kod novih konstrukcija; preporučujemo: PN...AOS.

Artikal

Naziv	DN	Veličina	col	Radni pritisak (bar)	D2 (mm)	L1 (mm)
PN 04 FS	5	3	3/16"	630,0	8,0	51,5
PN 06 FS 04	6	4	1/4"	630,0	8,0	58,5
PN 06 FS	6	4	1/4"	630,0	10,0	60,5
PN 06 FS 08	6	4	1/4"	630,0	12,0	59,5
PN 08 FS	8	5	5/16"	630,0	12,0	60,0
PN 10 FS	10	6	3/8"	630,0	14,0	66,0
PN 10 FS 13	10	6	3/8"	400,0	16,0	70,0
PN 13 FS 08	12	8	1/2"	400,0	12,0	61,5
PN 13 FS 10	12	8	1/2"	400,0	14,0	67,0
PN 13 FS	12	8	1/2"	400,0	16,0	70,0
PN 16 FS 13	16	10	5/8"	400,0	16,0	74,5
PN 16 FS	16	10	5/8"	400,0	20,0	78,5
PN 16 FS 20	16	10	5/8"	400,0	25,0	85,0
PN 20 FS 13	19	12	3/4"	400,0	16,0	79,5
PN 20 FS 16	19	12	3/4"	400,0	20,0	86,0
PN 20 FS	19	12	3/4"	400,0	25,0	90,0
PN 25 FS 20	25	16	1"	250,0	25,0	97,0
PN 25 FS	25	16	1"	250,0	30,0	102,0
PN 25 FS 32	25	16	1"	250,0	38,0	109,5
PN 32 FS 25	31	20	1.1/4"	250,0	30,0	113,0
PN 32 FS	31	20	1.1/4"	250,0	38,0	117,0
PN 40 FS 32	38	24	1.1/2"	250,0	38,0	120,5

Varijante proizvoda

PN FS VA Pritisna nazuvica, BES, plemeniti čelik