

Osobine

| | |
|---------------------------|----------------------------------|
| Oblast primene | za usisne i povratne crevovode |
| Konstrukcija | Obujmica sa zglobnim sprežnjakom |
| Norma | slično kao DIN 3017 |
| Materijal | čelik |
| Površinska zaštita | galvanska prevlaka |



Artikal

| Naziv | Opseg rastezanja (mm) | Širina trake (mm) |
|-------------|-----------------------|-------------------|
| MRS 17-19 | 17 - 19 | 18,0 |
| MRS 20-22 | 20 - 22 | 18,0 |
| MRS 21-23 | 21 - 23 | 18,0 |
| MRS 23-25 | 23 - 25 | 18,0 |
| MRS 25-27 | 25 - 27 | 18,0 |
| MRS 26-28 | 26 - 28 | 18,0 |
| MRS 29-31 | 29 - 31 | 18,0 |
| MRS 32-35 | 32 - 35 | 20,0 |
| MRS 36-39 | 36 - 39 | 20,0 |
| MRS 40-43 | 40 - 43 | 20,0 |
| MRS 44-47 | 44 - 47 | 22,0 |
| MRS 48-51 | 48 - 51 | 20,0 |
| MRS 52-55 | 52 - 55 | 22,0 |
| MRS 56-59 | 56 - 59 | 20,0 |
| MRS 60-63 | 60 - 63 | 20,0 |
| MRS 64-67 | 64 - 67 | 22,0 |
| MRS 68-73 | 68 - 73 | 24,0 |
| MRS 74-79 | 74 - 79 | 24,0 |
| MRS 80-85 | 80 - 85 | 24,0 |
| MRS 86-91 | 86 - 91 | 24,0 |
| MRS 92-97 | 92 - 97 | 24,0 |
| MRS 98-103 | 98 - 103 | 24,0 |
| MRS 104-112 | 104 - 112 | 24,0 |
| MRS 113-121 | 113 - 121 | 24,0 |
| MRS 122-130 | 122 - 130 | 25,0 |
| MRS 131-139 | 131 - 139 | 25,0 |
| MRS 140-148 | 140 - 148 | 25,0 |
| MRS 149-161 | 149 - 161 | 25,0 |
| MRS 162-174 | 162 - 174 | 25,0 |
| MRS 175-187 | 175 - 187 | 25,0 |
| MRS 188-200 | 188 - 200 | 25,0 |
| MRS 201-213 | 201 - 213 | 25,0 |
| MRS 214-226 | 214 - 226 | 25,0 |
| MRS 227-239 | 227 - 239 | 25,0 |
| MRS 240-252 | 240 - 252 | 25,0 |
| MRS 253-265 | 253 - 265 | 30,0 |
| MRS 266-278 | 266 - 278 | 30,0 |
| MRS 279-291 | 279 - 291 | 30,0 |
| MRS 292-304 | 292 - 304 | 30,0 |

Varijante proizvoda

MRSS Obujmica sa zglobnim sprežnjakom, Plemeniti čelik 1.4301